



ISO 8748 Spring steel
420-545 HV30 1,5X6MM

Article number	39150.015.006
Brand	-
UBB	950359066764
UNSPSC	31163201
EAN	8715492809438
PKG. of 200	Full Box Only

Technical Parameters

Diameter	1.5 mm
Length	6 mm
Material	Spring steel
Material technical	420-545 HV30

Standards

ISO	8748
DIN	7344

Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of coiled spring- type straight pins (spiral pins): These pins are used for connections or the positioning of two or more parts and may also be used as shafts and hinge- stop- or carrier pins, and are easily disassembled. Thanks
------	---

to their spiral shaped cross section (approximately 2.1/4 coils) these pins are very flexible and suitable for repeated use with dynamic loads. Equal stress distribution throughout their cross section against the hole wall produces a good press fit, which can absorb shear forces unaffected by the direction. The pins are chamfered at both ends, so they can easily be inserted and installed automatically.

Technical Specification

a ≈	0.5
d1 (max.)	1.71
d1 (min.)	1.61
d2 (max.)	1.4
D (mm)	1.5
L (mm)	6
V	1.9

Technical Drawing

