



## Parallel key high type DIN 6885 A Steel C45+C Plain 3X3X16MM

|                |               |
|----------------|---------------|
| Article number | 39250.033.016 |
| Brand          | -             |
| UBB            | 950359204464  |
| UNSPSC         | 31163207      |
| EAN            | 8715492812391 |
| PKG. of 50     | Full Box Only |

### Technical Parameters

|                    |                                                                 |
|--------------------|-----------------------------------------------------------------|
| Length             | 16 mm                                                           |
| Material           | Steel                                                           |
| Material technical | C45+C                                                           |
| Surface treatment  | Plain                                                           |
| Info               | Tolerance classes for dimensions b and h according to DIN 6880. |

### Standards

|     |        |
|-----|--------|
| NEN | 2430   |
| ISO | R773   |
| DIN | 6885-A |
| BS  | 4235-1 |

### Technical Specification

|                              |    |
|------------------------------|----|
| b                            | 3  |
| For shaft $\varnothing$      | 8  |
| For shaft $\varnothing \leq$ | 10 |
| h                            | 3  |
| L (mm)                       | 16 |

### Technical Drawing

