



Parallel key high type DIN 6885 A Steel C45+C Plain 4X4X50MM

Article number	39250.044.050
Brand	-
UBB	950359543531
UNSPSC	31163207
EAN	8715492812681
PKG. of 50	Full Box Only

Technical Parameters

Length	50 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

ISO	R773
DIN	6885-A
BS	4235-1
NEN	2430

Technical Specification

b	4
For shaft $\varnothing$	10
For shaft $\varnothing \leq$	12
h	4
L (mm)	50

Technical Drawing

