



Parallel key high type DIN 6885 A Steel C45+C Plain 12X8X56MM

Article number	39250.128.056
Brand	-
UBB	950359084171
UNSPSC	31163207
EAN	8715492814067
PKG. of 10	Full Box Only

Technical Parameters

Length	56 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

DIN	6885-A
ISO	R773
NEN	2430
BS	4235-1

Technical Specification

b	12
For shaft $\varnothing$	38
For shaft $\varnothing \leq$	44
h	8
L (mm)	56

Technical Drawing

