



Parallel key high type DIN 6885 A Steel C45+C Plain 14X9X40MM

Article number	39250.149.040
Brand	-
UBB	950359084908
UNSPSC	31163207
EAN	8715492814296
PKG. of 10	Full Box Only

Technical Parameters

Length	40 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

ISO	R773
BS	4235-1
NEN	2430
DIN	6885-A

Technical Specification

b	14
For shaft $\varnothing$	44
For shaft $\varnothing \leq$	50
h	9
L (mm)	40

Technical Drawing

