



Parallel key high type DIN 6885 A Steel C45+C Plain 16X10X160MM

Article number	39250.170.160
Brand	-
UBB	950359877186
UNSPSC	31163207
EAN	8715492814692
PKG. of 10	Full Box Only

Technical Parameters

Length	160 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

DIN	6885-A
NEN	2430
BS	4235-1
ISO	R773

Technical Specification

b	16
For shaft $\varnothing$	50
For shaft $\varnothing \leq$	58
h	10
L (mm)	160

Technical Drawing

