



Parallel key high type DIN 6885 A Steel C45+C Plain 22X14X80MM

Article number	39250.234.080
Brand	-
UBB	950359088396
UNSPSC	31163207
EAN	8715492815194
PKG. of 10	Full Box Only

Technical Parameters

Length	80 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

NEN	2430
DIN	6885-A
ISO	R773
BS	4235-1

Technical Specification

b	22
For shaft $\varnothing$	75
For shaft $\varnothing \leq$	85
h	14
L (mm)	80

Technical Drawing

