

Parallel key high type DIN 6885 A Steel C45+C Plain 22X14X125MM



Article number	39250.234.125
Brand	-
UBB	950359878663
UNSPSC	31163207
EAN	8715492815248
PKG. of 10	Full Box Only

Technical Parameters

b	22
h	14
Length (L) (mm)	125

Info Tolerance classes for dimensions b and h according to DIN 6880.

Material	Steel
Material technical	C45+C
Surface treatment	Plain

Technical Specification

For shaft $\varnothing >$	75
For shaft $\varnothing \leq$	85
h	14

Standards

ISO	R 773
DIN	6885 A
BS	4235-1

Technical Drawing

