



Split pin (cotter pin) DIN 94 Steel Zinc plated 1,2X36MM

Article number	39350.012.036
Brand	-
UBB	500645350520
UNSPSC	31163204
EAN	8717077082076
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	1.2 mm
Length	36 mm
Material	Steel
Surface treatment	Zinc plated

Standards

DIN	94
ISO	1234
NF	E25-774
NEN	182

Info	The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of the nominal length (L) is js17.
------	---

Technical Specification

a (max.)	2.5
----------	-----

Technical Drawing

b ≈	3
c (max.)	2
c (min.)	1.7
d (min.)	0.9
D (mm)	1.2
L (mm)	36
d (max.)	1

