



Split pin (cotter pin) DIN 94 Steel Zinc plated 13X180MM

Article number	39350.130.180
Brand	-
UBB	500644960659
UNSPSC	31163204
EAN	8717077045644
PKG. of 25	Full Box Only

Technical Parameters

Diameter	13 mm
Length	180 mm
Material	Steel
Surface treatment	Zinc plated

Standards

DIN	94
ISO	1234
NEN	182
NF	E25-774

Info	The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of the nominal length (L) is js17.
------	---

Technical Specification

a (max.)	6.3
----------	-----

Technical Drawing

b ≈	26
c (max.)	24.8
c (min.)	21.7
d (min.)	12.1
D (mm)	13
L (mm)	180
d (max.)	12.4

