



## Split pin (cotter pin) DIN 94 Steel Zinc plated 16X140MM

|                |               |
|----------------|---------------|
| Article number | 39350.160.140 |
| Brand          | -             |
| UBB            | 500644960998  |
| UNSPSC         | 31163204      |
| EAN            | 8717077045682 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                   |             |
|-------------------|-------------|
| Diameter          | 16 mm       |
| Length            | 140 mm      |
| Material          | Steel       |
| Surface treatment | Zinc plated |

### Standards

|     |         |
|-----|---------|
| ISO | 1234    |
| NEN | 182     |
| DIN | 94      |
| NF  | E25-774 |

|      |   |
|------|---|
| Info | The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of the nominal length (L) is js17. |
|------|---|

### Technical Specification

|          |     |
|----------|-----|
| a (max.) | 6.3 |
|----------|-----|

### Technical Drawing

|          |      |
|----------|------|
| b ≈      | 32   |
| c (max.) | 30.8 |
| c (min.) | 27   |
| d (min.) | 15.1 |
| D (mm)   | 16   |
| L (mm)   | 140  |
| d (max.) | 15.4 |

