



## Round head rivet DIN 660/124 Steel C4C/C10C Plain 2,5X8MM

|                |               |
|----------------|---------------|
| Article number | 39400.025.008 |
| Brand          | -             |
| UBB            | 500645354662  |
| UNSPSC         | 31162201      |
| EAN            | 8717077082557 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |            |
|--------------------|------------|
| Diameter           | 2.5 mm     |
| Length             | 8 mm       |
| Head shape         | Round head |
| Material           | Steel      |
| Material technical | C4C/C10C   |
| Surface treatment  | Plain      |

### Standards

|     |         |
|-----|---------|
| BS  | 4620    |
| DIN | 660/124 |
| ISO | 1051    |

### Technical Specification

|           |      |
|-----------|------|
| d1        | 2.5  |
| d2        | 4.4  |
| d3 (min.) | 2.37 |
| D (mm)    | 2.5  |
| e (max.)  | 1.25 |
| k (js14)  | 1.5  |
| L (mm)    | 8    |

### Technical Drawing

