



DIN 661/302 Steel C4C/C10C Plain 5X18MM

Article number	39410.050.018
Brand	-
UBB	500645360016
UNSPSC	31162201
EAN	8717077083097
PKG. of 500	Full Box Only

Technical Parameters

Diameter	5 mm
Length	18 mm
Head shape	Countersunk head
Material	Steel
Material technical	C4C/C10C
Surface treatment	Plain

Standards

BS	4620
DIN	661/302
ISO	1051

Technical Specification

d1	5
d2	8.8
d3 (min.)	4.82
D (mm)	5
e (max.)	2.5
k ≈	2.5
L (mm)	18

Technical Drawing

