



DIN 661/302 Steel C4C/C10C Plain 6X30MM

Article number	39410.060.030
Brand	-
UBB	950368044257
UNSPSC	31162201
EAN	8715492822277
PKG. of 250	Full Box Only

Technical Parameters

Diameter	6 mm
Length	30 mm
Head shape	Countersunk head
Material	Steel
Material technical	C4C/C10C
Surface treatment	Plain

Standards

DIN	661/302
ISO	1051
BS	4620

Technical Specification

d1	6
d2	10.5
d3 (min.)	5.82
D (mm)	6
e (max.)	3
k ≈	3
L (mm)	30

Technical Drawing

