



Grooved pin, full length parallel grooved with pilot DIN 1470 Free-cutting steel 5X40MM

Article number	39700.050.040
Brand	-
UBB	950359122112
UNSPSC	31163215
EAN	8715492823618
PKG. of 100	Full Box Only

Technical Parameters

Diameter	5 mm
Length	40 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

NEN	≈2601
DIN	1470
ISO	≈8739

Technical Specification

c ≈	0.6
d1	5
d2 ≈	5.25
D (mm)	5

Technical Drawing

L (mm)	40
r	5
Tolerance	h11
V	16.5

FABORY

