

Grooved pin, full length taper grooved DIN 1471 Free-cutting steel 3X12MM



Article number	39710.030.012
Brand	-
UBB	950359127244
UNSPSC	31163215
EAN	8715492824172
PKG. of 200	Full Box Only

Technical Parameters

d ₁	3
Diameter (mm)	3
Length (L) (mm)	12

Standards

DIN	1471
ISO	8744

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Technical Specification

c ≈	0.4
d ₂ ≈	3.25
r ≈	3
Tolerance	h9

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

