



Grooved pin, full length taper grooved DIN 1471 Free-cutting steel 4X40MM

Article number	39710.040.040
Brand	-
UBB	950359128564
UNSPSC	31163215
EAN	8715492824370
PKG. of 100	Full Box Only

Technical Parameters

d ₁	4
Diameter (mm)	4
Length (L) (mm)	40

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Standards

DIN	1471
ISO	8744

Technical Specification

c ≈	0.5
d ₂ ≈	4.25
r ≈	4
Tolerance	h11

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

