

Grooved pin, full length taper grooved DIN 1471 Free-cutting steel 8X12MM



Article number	39710.080.012
Brand	-
UBB	950359130602
UNSPSC	31163215
EAN	8715492824707
PKG. of 100	Full Box Only

Technical Parameters

d ₁	8
Diameter (mm)	8
Length (L) (mm)	12

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Standards

DIN	1471
ISO	8744

Technical Specification

c ≈	1
d ₂ ≈	8.35
r ≈	8
Tolerance	h11

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

