

Grooved pin, full length taper grooved DIN 1471 Free-cutting steel 8X45MM



Article number 39710.080.045

Brand -

UBB 950359131360

UNSPSC 31163215

EAN 8715492824776

PKG. of 100 Full Box Only

Technical Parameters

d ₁	8
Diameter (mm)	8
Length (L) (mm)	45

Standards

ISO	8744
DIN	1471

Info
 V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material Free-cutting steel

Technical Specification

c ≈	1
d ₂ ≈	8.35
r ≈	8
Tolerance	h11

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

