

Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 2,5X12MM



Article number	39720.025.012
Brand	-
UBB	950359133754
UNSPSC	31163215
EAN	8715492825070
PKG. of 200	Full Box Only

Technical Parameters

d ₁	2.5
Diameter (mm)	2.5
Length (L) (mm)	12

Standards

DIN	1472
ISO	8745

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Technical Specification

c ≈	0.3
d ₂ ≈	2.65
r ≈	2.5
Tolerance	h9

Technical Drawing

FABORY
OF COURSE.
SETTING THE STANDARD
IN FASTENING SOLUTIONS

