

## Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 4X24MM



Article number	39720.040.024
Brand	-
UBB	950359135577
UNSPSC	31163215
EAN	8715492825285
PKG. of 200	Full Box Only

### Technical Parameters

d <sub>1</sub>	4
Diameter (mm)	4
Length (L) (mm)	24

#### Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d<sub>2</sub> is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

### Standards

DIN	1472
ISO	8745

### Technical Specification

c ≈	0.5
d <sub>2</sub> ≈	4.25
r ≈	4
Tolerance	h11

### Technical Drawing

**FABORY** *OF COURSE.*  
SETTING THE STANDARD  
IN FASTENING SOLUTIONS

