

Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 5X24MM



Article number	39720.050.024
Brand	-
UBB	950359136492
UNSPSC	31163215
EAN	8715492825414
PKG. of 100	Full Box Only

Technical Parameters

d ₁	5
Diameter (mm)	5
Length (L) (mm)	24

Standards

ISO	8745
DIN	1472

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Technical Specification

c ≈	0.6
d ₂ ≈	5.3
r ≈	5
Tolerance	h11

Technical Drawing

FABORY *OF COURSE.*
SETTING THE STANDARD
IN FASTENING SOLUTIONS

