



Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 8X12MM

Article number	39720.080.012
Brand	-
UBB	950359137979
UNSPSC	31163215
EAN	8715492825575
PKG. of 100	Full Box Only

Technical Parameters

Diameter	8 mm
Length	12 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.


Standards

DIN	1472
NEN	≈2603
ISO	≈8745

Technical Specification

c ≈	1
d1	8
d2 ≈	8.35
D (mm)	8
L (mm)	12

Technical Drawing



$r \approx$

8

Tolerance

h11

V

40.5