



Grooved pin, full length parallel with chamfer DIN 1473 Free-cutting steel 2X30MM

Article number	39730.020.030
Brand	-
UBB	950359658479
UNSPSC	31163215
EAN	8715492825865
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2 mm
Length	30 mm
Material	Free-cutting steel
Info	V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Standards

ISO	≈8740
DIN	1473
NEN	≈2604

Technical Specification

c ≈	0.25
d1	2
d2 ≈	2.15
D (mm)	2

Technical Drawing

$f \approx$	0.9
$L \text{ (mm)}$	30
$r \approx$	2
Tolerance	h9
V	2.85

