



Brady Labels TLS2200 PTL-29-498 500PC

Article number	3T020953
Brand	-
UBB	500671740248
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	White
Width (mm)	38.1
Adhesive component	Repositionable Rubber
Basic material	Vinyl Cloth
Brady material number	B-498
Legend	Vinyl cloth Labels for M611, BMP61 and BMP71
Max. service temp. °C	80 °C
Max. wire/cable diameter (mm)	11.17
Min. service temp. °C	-40 °C
Print technology	Thermal Transfer
Printer compatibility	BMP61; BMP71; TLS2200; TLSPC LINK
Ribbon series	R6210
Vertical repeat (mm)	15.87
Compliance	UL Recognised
Performance characteristics	Abrasion Resistance;Low Temperature Resistance;Removable

Standards

Industry

FABORY

SETTING THE STANDARD
IN FASTENING SOLUTIONS

OF COURSE.

Data/
Telecommunications;
Electrical;
Healthcare:Laboratory

Content (pcs)	500
Finish	Semi gloss
Finish	Halbglanz
Finish	Semi lucios
Finish	Półmatowy
Finish	Semi brillo
Finish	Semi-brillant
Finish	Semi lesk
Finish	Zijdeglans
Finish	Fél fényes
Finish	Semi brilho
Finish	Semi lesk
Application method	Laboratory Identification; Wire & Cable Marking
Height (mm)	12.7
Length (L) (mm)	38.1
Model	CleanLift
Thickness	0.185
Type nr.	B-498
Weight (g)	184
Shape	Rectangle