



ABA Hose clamp Original, band width 12 mm Steel Zinc plated 50-65MM

Article number	43011.050.065
Brand	-
UBB	950553189198
UNSPSC	31162906
EAN	8715492830234
PKG. of 10	Full Box Only

Technical Parameters

Material	Steel
Surface treatment	Zinc plated

Standards

Technical Specification

Clamping range (mm)	50
S	1
Tightening torque approx. range (Nm)	5

Technical Drawing

