



ABA Heavy duty hose clamp
Robust Stainless steel AISI
430 51-55

Article number	43033.051.055
Brand	-
UBB	500571212660
UNSPSC	31162906
EAN	8715494138116
PKG. of 25	Full Box Only

Technical Parameters

Material	Stainless steel
Material technical	AISI 430
Info	Material type: band and bridging piece AISI 430 / screw and bolt steel zinc plated.Up to type 40-43 with hexagonal bolt M6x40, WAF 8 mm.Type 43-47 up to type 167-174 with hex socket screw M7x45 or M7x55, WAF 5 mm.Type 174-187 up to type 239-252 with hexagonal bolt M10x80, WAF 17 mm.ABA ROBUST is a heavy-duty hose clamp with rolled- up band edges. It is used primarely for tightening heavy- gauge reinforced hoses.

Standards

A	20
B	22.1
Clamping range (mm)	51
d	7
S	0.8
Type	51-55

