



Slotted cheese head screw DIN 84 Brass CU2/CU3 M1X5

Article number	48020.010.005
Brand	-
UBB	500645388900
UNSPSC	31161504
EAN	8717077095915
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1
Length	5 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

ISO	≈1207
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-127
NEN	≈1602
DIN	84

Technical Specification

d-D	M1
Thread length (min.)	25
dk (max.)	2
Full thread if L ≤	30
k (max.)	0.7
L (mm)	5
n	0.25
P	0.25
t (min.)	0.25

Technical Drawing