



Slotted cheese head screw DIN 84 Brass CU2/CU3 M1,4X10

Article number	48020.014.010
Brand	-
UBB	500645389817
UNSPSC	31161504
EAN	8717077096004
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.4
Length	10 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

NF	≈E25-127
DIN	84
NEN	≈1602
ISO	≈1207
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M1.4
Thread length (min.)	25
dk (max.)	2.6
Full thread if L ≤	30
k (max.)	0.9
L (mm)	10
n	0.3
P	0.3
t (min.)	0.4

Technical Drawing