



Slotted cheese head screw DIN 84 Brass CU2/CU3 M1,6X4

Article number	48020.016.004
Brand	-
UBB	500645390138
UNSPSC	31161504
EAN	8717077096035
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.6
Length	4 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

NF	≈E25-127
BS	≈4183
DIN	84
ISO	≈1207
ASME	≈B18.6.7M
NEN	≈1602

Technical Specification

d-D	M1.6
Thread length (min.)	25
dk (max.)	3
Full thread if L ≤	30
k (max.)	1
L (mm)	4
n	0.4
P	0.35
t (min.)	0.45

Technical Drawing