



Slotted cheese head screw DIN 84 Brass CU2/CU3 M1,6X5

Article number	48020.016.005
Brand	-
UBB	500645390211
UNSPSC	31161504
EAN	8717077096042
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.6
Length	5 mm
Driving features	Slotted
Head shape	Cylindrical head
Material	Brass
Material technical	CU2/CU3
Thread	Metric thread

Standards

ISO	≈1207
BS	≈4183
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127
DIN	84

Technical Specification

d-D	M1.6
Thread length (min.)	25
dk (max.)	3
Full thread if L ≤	30
k (max.)	1
L (mm)	5
n	0.4
P	0.35
t (min.)	0.45

Technical Drawing