



Slotted countersunk head screw DIN 963 A Brass CU2/ CU3 Nickel plated M3X25

Article number	48550.030.025
Brand	-
UBB	950353233105
UNSPSC	31161504
EAN	8715492853714
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Material technical	CU2/CU3
Surface treatment	Nickel plated
Thread	Metric thread

Standards

BS	≈4183
DIN	963
NEN	≈2370
NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	25
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

