



Slotted countersunk head screw DIN 963 A Brass CU2/ CU3 Nickel plated M3X35

Article number	48550.030.035
Brand	-
UBB	950353233360
UNSPSC	31161504
EAN	8715492853738
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	35 mm
Driving features	Slotted
Head shape	Countersunk head
Material	Brass
Material technical	CU2/CU3
Surface treatment	Nickel plated
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	35
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

