



Brady Roll UN Green UN30-DP-E 76CMX46M M

Article number	4G584968
Brand	-
UBB	500671874971
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Width (mm)	760
Legend	ROLL, Medium weight, double perforated & bonded 76 cm x 46 m
Industry	Beverage processing;Chemical;Food processing;Laboratory;Manufacturing;Maritime;Oil & gas;Pharmaceutical;Process;Warehouse & logistics
Basic material	2-ply, spunbound/meltblown, bonded
Capacity (absorption ltr)	147
Color	Green
Content (pcs)	5000
Height (mm)	760
Adhesive component	Permanent Acrylic
Perforation - lengthwise (mm)	38
Application method	Overspray; Leaks; Drips; In Drum & Liquid Storage Areas; Workstations; Laboratories.
Length (L) (mm)	760
Length (mtr)	46
Weight (g)	11600

Standards