



Round head rivet DIN 660/124 Brass CW508L 5X16MM

Article number	50200.050.016
Brand	-
UBB	500648068756
UNSPSC	31162201
EAN	8717077289895
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	5 mm
Length	16 mm
Head shape	Round head
Material	Brass
Material technical	CW508L

Standards

DIN	660/124
ISO	1051
BS	4620

Technical Specification

d1	5
d2	8.8
d3 (min.)	4.82
D (mm)	5
e (max.)	2.5
k (js14)	3
L (mm)	16

Technical Drawing

