



Split pin (cotter pin) DIN 94
Brass 6,3X100MM

Article number	50210.063.100
Brand	-
UBB	950359161623
UNSPSC	31163204
EAN	8715492242174
PKG. of 100	Full Box Only

Technical Parameters

Diameter	6.3 mm
Length	100 mm
Material	Brass
Info	The shape of the split pin ends are at the manufacturer's discretion.For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506.The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters.The tolerance class of the nominal length (L) is js17.

Standards

NEN	182
ISO	1234
NF	E25-774
DIN	94

Technical Specification

a (max.)	4
b \approx	12.6

Technical Drawing

c (max.)	11.8
c (min.)	10.3
d (min.)	5.7
D (mm)	6.3
L (mm)	100
d (max.)	5.9

