

Round head rivet DIN 660/124 Copper Cu-DHP 10X50MM



Article No.	50370.100.050
Brand	-
UBB	950368020802
UNSPSC	31162201
EAN	8715492246042
PKG. of 100	Full Box Only

Technical Parameters

d_1	10
Diameter (mm)	10
Length (L) (mm)	50
Head shape	Round head
Material	Copper
Material technical	Cu-DHP

Standards

ISO	1051
BS	4620
DIN	660/124

Technical Specification

d_2	16
d_3 (min.)	9.4
e (max.)	5
k (js14)	6.5

Technical Drawing

