



Split pin (cotter pin) DIN 94
Copper 3,2X40MM

Article number	50390.032.040
Brand	-
UBB	950359163868
UNSPSC	31163204
EAN	8715492246981
PKG. of 250	Full Box Only

Technical Parameters

Diameter	3.2 mm
Length	40 mm
Material	Copper

Info

The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of the nominal length (L) is js17.

Standards

ISO	1234
DIN	94
NF	E25-774
NEN	182

Technical Specification

a (max.)	3.2
b \approx	6.4

Technical Drawing

c (max.)	5.8
c (min.)	5.1
d (min.)	2.7
D (mm)	3.2
L (mm)	40
d (max.)	2.9

