

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M16X540

Article number	51000.160.450
Brand	-
UBB	500633213714
UNSPSC	31161620
EAN	8715494604932
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M16
Length	540 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	540
P	2
s	24

Technical Drawing

