

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M16X580

Article number	51000.160.580
Brand	-
UBB	500633214050
UNSPSC	31161620
EAN	8715494604963
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	580
Class	Min.50
Material	Stainless steel
Head shape	Hexagon head
Driving features	Hexagon
Thread direction	Right
Thread	Metric thread
Material technical	A2

Info
 Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	44
b (min.): L>200mm	57
b (min.): L≤125mm	38
k	10
P	2
s	24

Technical Drawing

