

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M20X210

Article number	51000.200.210
Brand	-
UBB	500571246585
UNSPSC	31161620
EAN	8715494127400
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	210 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	210
P	2.5
s	30

Technical Drawing

