

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M22X85

Article number	51000.220.085
Brand	-
UBB	500633112080
UNSPSC	31161620
EAN	8715494605045
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M22
Length	85 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	56
b (min.): L200mm	69
b (min.): L≤125mm	50
d-D	M22
k	14
L (mm)	85
P	2.5
s	32

Technical Drawing

