

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M24X200

Article number	51000.240.200
Brand	-
UBB	950351770397
UNSPSC	31161620
EAN	8715492252067
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	200 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	200
P	3
s	36

Technical Drawing

