

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M24X270

Article number	51000.240.270
Brand	-
UBB	500571247732
UNSPSC	31161620
EAN	8715494541213
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	270 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	270
P	3
s	36

Technical Drawing

