

Hexagon head screw DIN 933 Stainless steel A2 Min.50 M10X120

Article number	51010.100.120
Brand	-
UBB	951351786227
UNSPSC	31161620
EAN	8715492256195
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	120 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

ISO	4017
NEN	1568
NF	E25-114
ASME	B18.2.3.1M
DIN	933

Technical Specification

d-D	M10
k	6.4
L (mm)	120
P	1.5
s	17

Technical Drawing

