



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Stainless steel A2 70 M5X8**

Article number	51014.050.008
Brand	-
UBB	500634383573
UNSPSC	31161620
EAN	8715494555081
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

DIN	≈6921
EN	≈1665
ASME	≈B18.2.3.4M
ISO	≈4162

Technical Specification

d-D	M5
dc (max.)	11.8
k (max.)	5.4
L (mm)	8
P	0.8
s	8

Technical Drawing

