



**Hexagon flange bolt with  
serrated flange, DIN ≈6921  
Stainless steel A2 70 M5X10**

Article number	51014.050.010
Brand	-
UBB	500634383656
UNSPSC	31161620
EAN	8715494555111
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M5
Length	10 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info      Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

**Standards**

ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M
DIN	≈6921

Technical Specification

d-D	M5
dc (max.)	11.8
k (max.)	5.4
L (mm)	10
P	0.8
s	8

Technical Drawing

