



Hexagon flange bolt with serrated flange, DIN ≈6921 Stainless steel A2 70 M5X16

Article number	51014.050.016
Brand	-
UBB	500634383813
UNSPSC	31161620
EAN	8715494555197
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ASME	≈B18.2.3.4M
EN	≈1665
DIN	≈6921
ISO	≈4162

Info

Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Technical Specification

d-D	M5
dc (max.)	11.8
k (max.)	5.4
L (mm)	16
P	0.8
s	8

Technical Drawing

