



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Stainless steel A2 70 M8X12**

| | |
|----------------|---------------|
| Article number | 51014.080.012 |
| Brand | - |
| UBB | 500634385636 |
| UNSPSC | 31161620 |
| EAN | 8715494555838 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|--------------------|-----------------|
| Diameter | M8 |
| Length | 12 mm |
| Class | 70 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Stainless steel |
| Material technical | A2 |
| Thread direction | Right |
| Thread | Metric thread |

Info Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

| | |
|------|-------------|
| ASME | ≈B18.2.3.4M |
| ISO | ≈4162 |
| DIN | ≈6921 |
| EN | ≈1665 |

Technical Specification

| | |
|-----------|------|
| d-D | M8 |
| dc (max.) | 18 |
| k (max.) | 8.1 |
| L (mm) | 12 |
| P | 1.25 |
| s | 13 |

Technical Drawing

