



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Stainless steel A2 70 M8X50**

Article number	51014.080.050
Brand	-
UBB	500634386477
UNSPSC	31161620
EAN	8715494556149
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	50 mm
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M
DIN	≈6921

Technical Specification

d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	50
P	1.25
s	13

Technical Drawing

